


## PROPERTIES AND APPLICATIONS

Product	State	Colour	Poison class	Grain size	Deburring	Pre-polishing	Polishing	Fine polishing	Burnishing	Mirror finishing	Steel	Hardened steel	Stainless steel	Tungsten carbide	Non-ferrous metals	Aluminium	Zinc	Titanium	Ceramics	Precious metals	Plastics	
				my		Ra 0.4	Ra 0.4-0.2	Ra 0.2-0.1	Ra 0.1-0.05	Ra 0.025												
Delfinor Abrasiv 600	Powder	white	free	1	-	-	-	*	***	***	**	***	**	-	**	-	-	-	-	-	*	-
Delfinor Abrasiv 605	Powder	white	free	1	*	-	-	**	***	***	*	***	**	-	*	-	-	-	-	-	*	-
Delfinor Abrasiv 610	Powder	white	free	6	***	***	***	***	-	-	***	**	***	-	***	-	-	*	-	-	***	*
Delfinor Abrasiv 630	Powder	white	free	1	-	-	-	-	**	**	***	-	***	-	***	-	*	-	-	-	***	*
Delfinor Abrasiv 640	Powder	white	free	1	**	-	-	**	***	***	**	***	*	-	**	-	-	-	-	*	**	-
Delfinor Abrasiv 660	Powder	white	free	4	**	-	-	-	***	***	**	***	*	-	**	-	-	-	-	*	**	-
Delfinor Abrasiv 730	Powder	white	free	1	-	-	-	**	***	***	*	-	*	-	-	-	-	-	-	*	-	***
Delfinor Abrasiv 800	Powder	white	free	1	-	-	-	*	***	***	**	**	**	-	**	*	-	**	-	-	**	-
Delfinor Abrasiv BKD 600	Powder	black	free	8-10	***	***	***	**	-	-	***	***	***	***	*	-	-	-	-	**	*	-
Delfinor Abrasiv BKD 800	Powder	black	free	5.5-7.5	***	***	***	***	*	*	***	***	***	***	*	-	-	-	-	***	*	*
Delfinor Abrasiv BKD 1000	Powder	black	free	3-5	**	**	**	***	***	*	***	***	***	***	*	-	-	-	-	***	*	-
Delfinor Abrasiv BKD 1500	Powder	black	free	1.6-2.4	-	*	*	**	***	***	***	***	***	***	*	-	-	-	-	***	*	-
Delfinor Abrasiv EK 230	Powder	white	free	50-56	***	***	*	-	-	-	***	*	***	-	***	***	***	***	***	-	**	-
Delfinor Abrasiv EK 400	Powder	white	free	16-18	***	***	**	-	-	-	***	*	***	-	***	***	***	***	***	-	**	-
Delfinor Abrasiv GS 120	Powder	green	free	88-125	***	**	*	-	-	-	**	-	**	-	***	**	**	***	-	-	*	-
Delfinor Abrasiv GS 300	Powder	green	free	30-35	***	***	***	**	-	-	**	-	**	-	***	**	**	***	-	-	**	-
Delfinor Abrasiv K 120	Powder	grey	free	90-125	***	**	*	-	-	-	**	-	**	-	*	**	**	*	*	-	-	-
Delfinor Abrasiv K 220	Powder	grey	free	40-70	***	***	*	-	-	-	***	*	**	-	*	*	*	*	*	-	-	-
Delfinor Abrasiv SD 280	Powder	grey	free	35-38	***	***	-	-	-	-	***	***	***	**	*	-	-	-	-	*	-	-
Delfinor Abrasiv SD 400	Powder	grey	free	16-18	***	***	**	-	-	-	***	***	***	**	*	-	-	*	**	*	*	-
Delfinor Abrasiv SD 600	Powder	grey	free	8-10	***	***	***	**	-	-	***	***	***	**	*	-	-	*	**	*	*	-
Delfinor Abrasiv SD 1000	Powder	grey	free	3.7-5.3	***	***	***	**	-	-	***	***	***	**	***	-	-	*	**	*	*	-
Delfinor Abrasiv TL	Powder	orange	free	5	*	*	*	***	**	*	**	-	***	-	-	-	-	-	-	-	-	**
Delfinor Diamant 0.0005	Powder	grey	free	0.5	-	-	-	-	***	***	-	*	-	***	*	-	-	-	-	***	*	-
Delfinor Diamant 0.0001	Powder	orange	free	1	-	-	-	-	***	***	-	*	-	***	-	-	-	-	-	***	*	-
Burnishing paste PP20	Paste	white	free	1	-	-	-	-	***	***	***	*	***	-	***	*	**	-	-	-	***	-
Burnishing paste PP30	Powder	grey	free	1	-	-	-	-	***	***	*	-	**	-	***	*	*	-	-	-	***	-
Burnishing paste PP40	Paste	white	free	1	-	-	-	-	***	***	*	-	***	-	-	*	*	-	-	-	-	-
Burnishing paste PP50	Paste	white	free	1	-	-	-	-	***	***	-	-	*	-	***	-	-	-	-	-	*	-

- Unsuitable | \* Conditionally suitable | \*\* good | \*\*\* very good Note: Pre-polishing or fine polishing may be required before the burnishing process.



**AVERAGE MATERIAL REMOVAL (GRAMS)  
PER TIME UNIT (HOURS)**

